



**HiMark®**

Flexible // Dependable

OFFICIAL REPRESENTATIVE:



**PLASTRADE Packaging Kft.**  
H-1025 Budapest, Szépvölgyi út 52.  
HUNGARY  
☎ +36 1 886 9225  
☎ +36 1 886 9226  
✉ [plastrade@plastrade.hu](mailto:plastrade@plastrade.hu)  
🌐 [www.plastrade.hu](http://www.plastrade.hu)

One of our most versatile pumps, HiMark® is suitable for a wide range of products, including difficult, viscous and aggressive formulations. It comes available in a wide range of dimensions, finishes, spray angles and outputs for a truly custom solution. And, with a child-resistant option, you can add an additional layer of safety while still ensuring an easy ergonomic experience.



# HiMark®

## Metered dispensing that goes the distance

- Versatile product range with many options for outputs, closures and adapters
- Easily customised with numerous aesthetic options
- Topical, oral and nasal options available<sup>1</sup>
- Dose counter and safety clip options available
- Drug Master File DMF #28564
- Suitable for non-drip nasal sprays and other viscous formulations
- Wide output range with many options
- For aggressive products, alternative materials can be provided for critical pump components
- Child-resistant option available



### Adapters

Nasal,  
Oral,  
Topical,  
Ear



ERF 20



Dose counter



Plastiape NA<sup>2</sup>



MTA5



ATA 19-M



Throat adapter medium



SATA




NM 2<sup>2</sup>




NM 3<sup>2</sup>



NM 17<sup>2</sup>



NM 170<sup>2</sup>



ER 13




ER 15



ERT 13<sup>3</sup>



ERT 15<sup>3</sup>



ER 25<sup>4</sup>



ERM (cream)



Ear adapter

### Closures



Screw: AVL  
(15-415, 18-415,  
EUR 5)



Screw: AVZ (18-415, DIN 18,  
BV-2 PP18, 20-410, BV-111,  
Pharma 22 Special, EUR 5,  
22-415, 24-410, 24-415)



Screw: AVLG  
(15-415, 18-415, 20-410,  
20-415, EUR 5, 22-410,  
22-415, 24-410, 24-415)



Ferrule  
(13 mm, 15 mm,  
18 mm, 20 mm)



Crimp  
(PL 1")

### Overcaps



ST



CT

### Options



Safety clip

### Output

0.050 ml, 0.070 ml,  
0.100 ml, 0.130 ml,  
0.190 ml

- <sup>1</sup> some adapters require manual assembly
- <sup>2</sup> available through partner
- <sup>3</sup> shown with C3 insert
- <sup>4</sup> compatible with PL pumps

Cross-sectional drawing for  
HiMark is available at [silgandispensing.com](http://silgandispensing.com)